

Because of all the technology packed into the ebode LightSpeaker™, it is much larger than a normal light bulb, both in length and width.

The best way to use ebode Lightspeaker™ is in a lampshade where you cannot actually see the sides of the product at all. As long as the front grille is unrestricted so you can hear the music and see the light, you do not really want to see where the sound and light comes from. In general this means that the ideal is a long, slim lampshade rather than one short and wide.

Please give this some thought when choosing a lampshade for your ebode LightSpeakers™. Of course, when your existing lampshades are large enough to accommodate the ebode LightSpeakers™, you can use these.

Please note - between the front edge of the E27 socket in your fitting and the front Grille of ebode Light-Speaker™ you need to have a shade/fitting that will be at least 15 cm long and 14 cm wide

Let's face it - everyone loves to shop at IKEA*! We have found that the following selection of their models work with the ebode LightSpeakers™.

Lampshades



Erserud - multiple prints (34cm)



Stycke - multiple prints (34cm)



Skimra - multiple prints and colours (19cm)



Klavsta - multiple prints (40cm)



Gnejs - in two colours (34cm)



Ekas - in two colours (34cm)

*IKEA is a registered trademark of Inter-IKEA Systems B.V. This file is intended as a source of information for those interested in using ebode LightSpeakers™ with IKEA lamps. We are not affiliated with IKEA in any way. ebode LightSpeaker™ fitted the indicated lamps at the time of testing, we cannot be held responsible for any changes to the IKEA products.

Because of all the technology packed into the ebode LightSpeaker™, it is much larger than a normal light bulb, both in length and width.

The best way to use ebode Lightspeaker™ is in a lampshade where you cannot actually see the sides of the product at all. As long as the front grille is unrestricted so you can hear the music and see the light, you do not really want to see where the sound and light comes from. In general this means that the ideal is a long, slim lampshade rather than one short and wide.

Please give this some thought when choosing a lampshade for your ebode LightSpeakers™. Of course, when your existing lampshades are large enough to accommodate the ebode LightSpeakers™, you can use these.

Please note - between the front edge of the E27 socket in your fitting and the front Grille of ebode Light-Speaker™ you need to have a shade/fitting that will be at least 15 cm long and 14 cm wide

Let's face it - everyone loves to shop at IKEA*! We have found that the following selection of their models work with the ebode LightSpeakers™.

Hanging lamps



365+ Lunta (20 cm diameter, 43 cm h)



Orgel (22cm w, 31cm h)

Floor Standing Lamps



Januari (134cm h)



Along (68-81cm h)



Orgel (148 cm h)

Table Lamps



Asele (45 cm diameter, 55,5 cm h)



Januari (35 cm h)

Pendel



Hemma

*IKEA is a registered trademark of Inter-IKEA Systems B.V. This file is intended as a source of information for those interested in using ebode LightSpeakers™ with IKEA lamps. We are not affiliated with IKEA in any way. ebode LightSpeaker™ fitted the indicated lamps at the time of testing, we cannot be held responsible for any changes to the IKEA products.